


Micro-Fraises
Micro end mills
Mikrofräser


215-R



Ød1e8	l1	R	ØDh6	L	Rev. TiALN
0.20	0.30	0.10	3	39	☑
0.25	0.35	0.125	3	39	☑
0.30	0.45	0.15	3	39	☑
0.40	0.60	0.20	3	39	☑
0.50	0.75	0.25	3	39	☑
0.60	0.90	0.30	3	39	☑
0.70	1.05	0.35	3	39	☑
0.80	1.20	0.40	3	39	☑
0.90	1.35	0.45	3	39	☑
1.00	1.50	0.50	3	39	☑
1.10	1.65	0.55	3	39	☑
1.20	1.80	0.60	3	39	☑
1.30	1.95	0.65	3	39	☑
1.40	2.10	0.70	3	39	☑
1.50	2.25	0.75	3	39	☑
1.60	2.40	0.80	3	39	☑
1.80	2.70	0.90	3	39	☑
2.00	3.00	1.00	3	39	☑


2 dents – Hémisphérique
 2 teeth – With ball end
 2 Zähne – Halbkugel Form

$l1 = 1.5 \times \varnothing$



Micro-Fraises
Micro end mills
Mikrofräser

230-R



Ød1e8	l1	R	ØDh6	L	Rev. TiALN
0.30	1.00	0.15	3	39	☑
0.40	1.00	0.20	3	39	☑
0.50	1.50	0.25	3	39	☑
0.60	1.50	0.30	3	39	☑
0.70	2.00	0.35	3	39	☑
0.80	2.00	0.40	3	39	☑
0.90	2.50	0.45	3	39	☑
1.00	3.00	0.50	3	39	☑
1.20	4.00	0.60	3	39	☑
1.40	4.00	0.70	3	39	☑
1.50	4.00	0.75	3	39	☑
1.60	4.00	0.80	3	39	☑
1.80	5.00	0.90	3	39	☑
2.00	6.00	1.00	3	39	☑
2.10	6.00	1.05	3	39	☑
2.20	6.00	1.10	3	39	☑
2.50	7.00	1.25	3	39	☑
2.80	7.00	1.40	3	39	☑

2 dents – Hémisphérique
 2 teeth – With ball end
 2 Zähne – Halbkugel Form

$l1 = 3 \times \varnothing$

